

Announcing the NEW Poroshell 120



Poroshell gives you the benefits of sub-two-micron performance on existing standard LCs.

- Sub-2 μm -like high efficiency
- At ~ 40-50% lower pressure
- 2.7 μm particle size
- A "standard" frit to reduce potential clogging
- The particle has a solid core (1.7 μm) and porous outer layer (1.0 μm with a 0.5 μm diffusion path)

And for a limited time 40 % off your first Agilent Poroshell Column

For a limited time, save 40 % on your first Agilent Poroshell column. Promotion valid in Europe, Middle East, Africa and India. Expires April 31st 2010. Use Promotion Code SHELL10 when ordering.

Zarejestruj się już dzisiaj!

1. [Kalendarium na stronie
www.perlan.com.pl](http://www.perlan.com.pl)

2. Fax: 022 54 91 401

E-mail: jcwyl@perlan.com.pl

Name _____

Title _____

Company _____

Address _____

Postal Code / City _____

Phone _____

Fax _____

Email address _____

Yes, I would like to receive e-mail updates from Agilent on related products and services

Upon registration for this seminar a confirmation letter will be sent to you via email. Please provide you email address. If you prefer, confirmation can be sent via fax.

KARTA ZGŁOSZENIOWA WROCLAW

**Termin seminarium, lokalizacja
oraz warunki uczestnictwa.**

27 kwietnia 2010

Wrocław

Hotel Scandic

Plac Marszałka Józefa

Piłsudskiego

Wrocław

(071) 787 01 43

Zgłoszenie należy odesłać

do:

15 kwietnia 2010

Liczba miejsc jest
ograniczona.

Udział w Seminarium jest
bezpłatny.

Arriving soon at a city near you!
www.agilent.com/chem/LCTIPS_Europe